

<u>LXT</u>



# Compact & Lightweight

Photo:DST421



DST421 4 mm J Wire Stapler



DS121 10 mm J Wire Stapler



Superior in work volume on a single full battery charge

Work amount per charge: About 4,80 staples



Net weight 2.5 kg battery: BL1850B

# Staple Length 13-25mm

30%

**Quicker fire response** thanks to electronically controlled contact arm.

Photo : DST421



**Remaining staple** view window







**Compact overall length** 

al state

Photo: DST121



For DST421

No.	Part Number	Description
1	B-04400	STAPLE 4X10-410J
2	B-04416	STAPLE 4X13-413J
3	B-04422	STAPLE 4X16-416J
4	B-04438	STAPLE 4X19-419J
5	B-04444	STAPLE 4X22-422J
6	B-04450	STAPLE 4X25-425J

#### For DST121

No.	Part Number	Description
1	B-04466	STAPLE 10X10-1010J
2	B-04472	STAPLE 10X13-1013J
3	B-04488	STAPLE 10X16-1016J
4	B-04494	STAPLE 10X19-1019J
5	B-04503	STAPLE 10X22-1022J
6	B-04519	STAPLE 10X25-1025J

## **Makita Singapore Pte Ltd**

7, Changi South Street 3, Singapore 486348 Phone: +65-6546-8700 Fax: +65-6546-8711 Email : msgproductteam@makita.com.sg Website : www.makita.com.sg Facebook : www.facebook.com/MakitaSG



Piston Counterweight

## Cordless Stapler DST421 / DST121

		DST421	DST121
Depth Adjustment	Staple	Width: 4 mm (N/A")	Width: 10 mm (N/A")
		Length: 13 - 25 mm (1/2" - 1")	Length: 13 - 25 mm (1/2" - 1")
🔀 Auto Firing Stop		Size: 1.2 x 0.6 mm	Size: 1.2 x 0.6 mm
	Magazine capacity	100	100
🚵 Anti Vibration	Shot q'ty on a single	w/ BL1860B: 4,800	w/ BL1860B: 4,800
,	full battery charge		
🔆 Built-in Job Light	Dimensions	w/ BL1815N: 244x79x216	w/ BL1815N: 244x79x216 mm
	$(L \times W \times H)$	mm (9-5/8"x3-1/8"x8-1/2")	(9-5/8"x3-1/8"x8-1/2")
Carrying Case		w/BL1830B/BL1850B/	w/ BL1830B / BL1850B /
		BL1860B: 260x79x216 mm	BL1860B: 260x79x216 mm
		(10-1/4"x3-1/8"x8-1/2")	(10-1/4"x3-1/8"x8-1/2")
	Net weight	2.2 - 2.5 kg (4.9 - 5.5 lbs.)	2.2 - 2.5 kg (4.9 - 5.5 lbs.)
tandard Equipment : Safe	ety Goggles, Nose Adapte	er, Belt Clip, Battery, Charger	

The weight may differ depending on the attachment(s), including the battery cartridge. The lightest and heaviest combination, according to EPTA-Procedure 01/2014, are shown in the table. Items of standard equipment and specifications may vary by country or area





VISIT OUR WEBSITE



DOWNLOAD LEAFLET